

Junior Tip Cleaner

Ask for a demo



Search ▼

This automatic cleaner improves thermal transfer of the tip in only 1 second, which means you save time and optimize production.

The operator just needs to press the button of the opening with the tool and two motorized brushes will clean the tip. It is also possible to select the continuous mode.

The splashguard helps keep the bench always clean and free of Foreign Object Debris (FOD).

The CLMS-B can be fitted into any work area thanks to its reduced size and it is very easy to maintain. The solder collector tray can be emptied and re-used with no wear and tear.



PRODUCT COMPOSITION

1 CLMS-A8 Brushes for CLMS

SPECIFICATIONS

Operating modesSwitch and continuousBrush diameterØ 34 mm (1.33 in)

Brush speed 550 rpm

650 rpm (continuous mode)

Silent operation 30 dB at 30 cm

Ambient operating temp. 10 to 40 °C / 50 to 104 °F

11.01.2021 17:39

CONNECTIVITY **Equipotential bonding**

ESD/EOS ESD safe AC adapter

Input: 100-240 V, 50/60 Hz Output: DC 12 V, 1 A

DIMENSIONS AND WEIGHT

Cleaning unit 95 x 91 x 112 mm / 1.45 Kg

3.74 x 3.58 x 4.41 in / 3.20 lb

220 x 135 x 125 mm / 1.63 Kg Package

CONNECTABLES

Consumables



CLMS-A8

Brushes for CLMS

11.01.2021 17:39 2/2